

## TARAPOREVALA MARINE BIOLOGICAL RESEARCH STATION

(Dr. B.S. Konkan Krishi Vidyapeeth, Dapoli)
3<sup>rd</sup> Floor, New Administrative Building, Bandra (E), Mumbai 400051.
Tel/Fax: (022) 26516816; E-mail. tmbrs@rediffmail.com

No. TMBRS/DBSKKV/Spectrophotometer/ 357/2021. Dated: 17 SEP 2021

To,
The Director of Extension Education,
Dr. B.S. Konkan Krishi Vidyapeeth,
Dapoli – 415712.
Dist. Ratnagiri

Sub: Publishing of quotation calling notices for purchase of **UV Single Beam Spectrophotometer Model: PLS 295** at Taraporevala Marine Biological Research Station, Bandra, Mumbai...

Ref: No. DBSKKV/ RES-II/1835/6947/2021, dt. 06.09.2021.

Sir,

With reference to above cited subject, it is requested to kindly arrange to publish the quotation calling notices for supply of **UV Single Beam Spectrophotometer Model: PLS 295** including specifications, quantities and accessories etc. on the University website. The materials will be purchased by the Taraporevala Marine Biological Research Station, Bandra, Mumbai.

Thanking you,

Yours faithfully,

RESEARCH OFFICER

Copy submitted with compliments to:

The Manager, Agriculture Knowledge Management Unit (AKMU)
 (akmudbskkv@gmail.com), DBSKKV, Dapoli, with a request to publish attached
 'quotation calling' notices on the university website: www.dbskk.org



## TARAPOREVALA MARINE BIOLOGICAL RESEARCH STATION

(Dr. B.S. Konkan Krishi Vidyapeeth, Dapoli)
3<sup>rd</sup> Floor, New Administrative Building, Bandra (E), Mumbai 400051.
Tel/Fax: (022) 26516816; E-mail. tmbrs@rediffmail.com

No. TM	IBRS/QUOTATION / Spectrophotometer //2021.	Dated:	17	SEP	2021
Sub:	Supply of quotations for UV Single beam Spectrophotometer (P	LS – 295)			

Sir/Madam,

This office is desirous of purchasing / fabricating and installing of a UV Single beam Spectrophotometer (PLS - 295) for laboratory purpose. The specifications of the same are enclosed along-with. You are requested to quote your competitive rates, item - wise for the purchase/supply and installation etc in detail, as per the below mentioned terms and conditions:

## **Terms & Conditions:**

- Quotation should be sent in a closed Envelope super scribing "Quotation for the purchase of UV Single beam Spectrophotometer (PLS 295)" by post or courier only. Hand delivery of the quotations will not be accepted.
- 2. The quotation should clearly state the Basic price, applicable taxes and other charges if any. It is necessary to mention **GST number** on quotations.
- 3. Only those items whose physical delivery can be effected within should be included. Quotation must bear written declaration to the effect.
- 4. Terms and conditions regarding payment, delivery and guarantee should be mentioned clearly. However, the delivery of the material should be sent to: Research Officer, Taraporevala Marine Biological Research Station, 3<sup>rd</sup> Floor, Administrative Building, Bandra (E), Mumbai 400051; and your payment will be made against the delivery. Please note that any Bank formalities will not be accepted.
- 5. The Demand Draft Commission as well as postage regarding Payment is to be borne by the supplier.
- 6. The delivery should be FOR Destination (as the Research Station/College is situated in the Municipal limits 'Octrai' is not applicable).
- 7. If you are the Sole Manufacturer or appointed as an Authorized Dealer for the sale, please enclose a copy of certificate stating as Sole Manufacturer / Authorized Dealer.
- 8. The undersigned reserves the right to reject / withdraw/correct the content/ or to extend the date of acceptance for any or all quotations without giving any reason thereof.
- 9. Quotation complete in above details should be sent on or before 08.10.2021, by 05:00PM, to:

The Research Officer,
Taraporevala Marine Biological Research Station,
3rd Floor, New Administrative Building, Bandra (E), Mumbai, (MS) – 400 051.
Yours sincerely,

Encl: detailed specifications,

Research Officer

## Copy submitted to the:

- 1. The Director of Research, Dr.B.S. Konkan Krishi Vidyapeeth, Dapoli, Dist. Ratnagiri.
- 2. The Director of Extension, Dr.B.S. Konkan Krishi Vidyapeeth, Dapoli, Dist. Ratnagiri.
- 3. The Manager, Agriculture Knowledge Management Unit (AKMU), DBSKKV, Dapoli.
  - You are requested to publish said "Quotation Calling" letter/advertisement on the University website: www.dbskkv.org.
- 4. Notice Board, TMBRS, Mumbai

Iodel: PLS 295 Iodel: PLS 295 Ionsisting of: Wavelength Range: 190–1000 nm Spectral Bandwidth: 2 nm Optical System: Single Beam. Wavelength Accuracy: +/- 1nm Wavelength Repeatability: 0.5 nm Wavelength Setting: Auto Photometric Accuracy: +/-0.5% T Photometric Repeatability: 0.3% T Photometric Range: -0.3 – 3A, 0 – 200%T Stability: +/- 0.002A/h @500nm Stray Light: ≤ 0.3%T Display: 124 X 64Dots LCD Display Detector: Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	required 2
Wavelength Range: 190–1000 nm  Spectral Bandwidth: 2 nm  Optical System: Single Beam.  Wavelength Accuracy: +/- 1nm  Wavelength Repeatability: 0.5 nm  Wavelength Setting: Auto  Photometric Accuracy: +/-0.5% T  Photometric Repeatability: 0.3% T  Photometric Range: - 0.3 – 3A, 0 – 200%T  Stability: +/- 0.002A/h @500nm  Stray Light: ≤ 0.3%T  Display: 124 X 64Dots LCD Display  Detector: Silicon Photo Diode  Standard Cell Holder: 4 Position 10mm Cell Changer.	
Wavelength Range: 190–1000 nm  Spectral Bandwidth: 2 nm  Optical System: Single Beam.  Wavelength Accuracy: +/- 1nm  Wavelength Repeatability: 0.5 nm  Wavelength Setting: Auto  Photometric Accuracy: +/-0.5% T  Photometric Repeatability: 0.3% T  Photometric Range: - 0.3 – 3A, 0 – 200%T  Stability: +/- 0.002A/h @500nm  Stray Light: ≤ 0.3%T  Display: 124 X 64Dots LCD Display  Detector: Silicon Photo Diode  Standard Cell Holder: 4 Position 10mm Cell Changer.	
Spectral Bandwidth: 2 nm Optical System: Single Beam. Wavelength Accuracy: +/- 1nm Wavelength Repeatability: 0.5 nm Wavelength Setting: Auto Photometric Accuracy: +/-0.5% T Photometric Repeatability: 0.3% T Photometric Range: - 0.3 - 3A, 0 - 200%T Stability: +/- 0.002A/h @500nm Stray Light: ≤ 0.3%T Display: 124 X 64Dots LCD Display Detector: Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Optical System: Single Beam.  Wavelength Accuracy: +/- 1nm  Wavelength Repeatability: 0.5 nm  Wavelength Setting: Auto  Photometric Accuracy: +/-0.5% T  Photometric Repeatability: 0.3% T  Photometric Range: -0.3 - 3A, 0 - 200%T  Stability: +/- 0.002A/h @500nm  Stray Light: ≤ 0.3%T  Display: 124 X 64Dots LCD Display  Detector: Silicon Photo Diode  Standard Cell Holder: 4 Position 10mm Cell Changer.	
Wavelength Accuracy: +/- 1nm  Wavelength Repeatability: 0.5 nm  Wavelength Setting: Auto  Photometric Accuracy: +/-0.5% T  Photometric Repeatability: 0.3% T  Photometric Range: - 0.3 – 3A, 0 – 200%T  Stability: +/- 0.002A/h @500nm  Stray Light: ≤ 0.3%T  Display: 124 X 64Dots LCD Display  Detector: Silicon Photo Diode  Standard Cell Holder: 4 Position 10mm Cell Changer.	
Wavelength Repeatability: 0.5 nm  Wavelength Setting: Auto  Photometric Accuracy: +/-0.5% T  Photometric Repeatability: 0.3% T  Photometric Range: - 0.3 - 3A, 0 - 200%T  Stability: +/- 0.002A/h @500nm  Stray Light: ≤ 0.3%T  Display: 124 X 64Dots LCD Display  Detector: Silicon Photo Diode  Standard Cell Holder: 4 Position 10mm Cell Changer.	
Wavelength Setting: Auto Photometric Accuracy: +/-0.5% T Photometric Repeatability: 0.3% T Photometric Range: -0.3 - 3A, 0 - 200%T Stability: +/-0.002A/h @500nm Stray Light: ≤ 0.3%T Display: 124 X 64Dots LCD Display Detector: Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Photometric Accuracy: +/-0.5% T Photometric Repeatability: 0.3% T Photometric Range: - 0.3 – 3A, 0 – 200%T Stability: +/- 0.002A/h @500nm Stray Light: ≤ 0.3%T Display: 124 X 64Dots LCD Display Detector: Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Photometric Repeatability: 0.3% T Photometric Range: - 0.3 – 3A, 0 – 200%T Stability: +/- 0.002A/h @500nm Stray Light: ≤ 0.3%T Display: 124 X 64Dots LCD Display Detector: Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Photometric Range: - 0.3 – 3A, 0 – 200%T Stability: +/- 0.002A/h @500nm Stray Light: ≤ 0.3%T Display: 124 X 64Dots LCD Display Detector: Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Stability: +/- 0.002A/h @500nm Stray Light: ≤ 0.3%T Display: 124 X 64Dots LCD Display Detector: Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Stray Light: ≤ 0.3%T Display: 124 X 64Dots LCD Display Detector: Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Display : 124 X 64Dots LCD Display Detector : Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Detector : Silicon Photo Diode Standard Cell Holder: 4 Position 10mm Cell Changer.	
Standard Cell Holder: 4 Position 10mm Cell Changer.	
Light Source : Tungsten & Dueterium Lamp	
Out Put : USB & Parallel Port (Printer)	
Power Requirement: 230V AC 50Hz.	
Accessories:	
<ul> <li>Accessory Kit Including 4 Glass Cell 1cm - 1No,</li> </ul>	
· · · · · · · · · · · · · · · · · · ·	
- DUILWAI C MAILUAI.	
	<ul> <li>2 Quartz Cell (1 cm) - 1 No.</li> <li>Software CD,</li> <li>Software Key,</li> <li>USB Cable,</li> <li>Power Cable,</li> <li>Software Manual,</li> <li>Dust Cover</li> </ul>

Principal Investigator